RS232 Interface



With this option, TECHNIX power supplies can be controlled via RS232.



The "L.A.B.TEC" (Laboratory Analog Board Technix) is designed to run without damages and control losses in very difficult environments as repetitive electrical arcs, parasitic atmospheres...

Micro-controller is fully protected from the random events produced on the output voltage and wich are generally responsible for the micro-controllers resets.

The board is made with a shielded structure and with special components acting as a complete protection.

RS232 BOARD

- Specialy design for HV environment
- Multilayer PCB
- Remotely control your generator with PC or
- Labview runtime available (option)
- 9600 Bauds, full-duplex
- ASCII protocol
- 12 Bits resolution
- 10 Hz Bandwith






With RS232 Option

Control via COM-Port Any device with a RS232 com port can drive the generator.

Compatible with LABVIEW untime (optional)



- User gets on his PC the image of the generator front panel
- Settings and controls available like they should be on the front panel
- All the functionality of the standard front panel:
 - **Setting and Display of Voltage and Current**
 - Indicators: HVon, HVoff, Voltage/Current Regulation, Line, Fault, Interlock, Remote mode
 - Preset & OCP/OCL functions
 - **HVon, HVoff control**
 - Inhibit
 - Histograms & Measurement savings

Reference: LABVIEW

Reference: RS232